FD4S-B144J00DBB4



FDH 4000, 144 distribution fibers, no splitters loaded, SC/APC, dielectric, ribbon, 100 ft stub

- Thermoplastic construction provides UV stabilization, flame retardancy, and chemical & impact resistance
- Provides air/water tight seal ensuring protection from flooding and fungus
- Unsurpassed reliability makes it ideal for aerial and below grade applications
- Supports diverse Plug-and-Play splitter and xWDM module Configurations

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber distribution closure

Product Series FDH 4000

General Specifications

Access Front

Cable TypeDielectric - Stranded

ColorBlackDistribution Ports, quantity144Fibers per Feeder Cable, quantity72Interface, InputSC

Interface Feature, Input APC

Mounting Handhole | Pole | Wall

Splitter Slots, quantity 5

Dimensions

 Height
 812.8 mm | 32 in

 Width
 241.3 mm | 9.5 in


 Cable Length
 30.48 m | 100 ft


Enclosure Size Small


Dimension Drawing



FD4S-B144J00DBB4








Ordering Tree

FD4S-B144J00DBB4



Environmental Specifications

Environmental Space Above ground | Aerial | Below ground

Qualification Standards IEC 60529, IP68 | Telcordia GR-3121-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Weight, net 15.876 kg | 35 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



COMMSCOPE®