

MX6-SPL6030-1440-D



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 2.2 mts

Replaced By:

MX6-SPL6030-A-D7Z4 OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 7 ft

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Fiber entrance cabinet
Product Brand	OMX600®
Product Series	OMX

General Specifications

Access	Front
Cable Entry Location	Bottom
Cable Exit Location	Bottom
Color	Putty white
Mounting	Raised floor
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184

Dimensions

Height	2200 mm 86.614 in
Width	600 mm 23.622 in
Depth	300 mm 11.811 in

Environmental Specifications

Environmental Space	Indoor
---------------------	--------

MX6-SPL6030-1440-D

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

