# FBWSCUC11

#### **Base Product**



### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America
Portfolio	CommScope®
Product Type	Fiber pigtail, unjacketed
Product Brand	SYSTIMAX InstaPATCH® 360
Product Series	FBW
Ordering Note	Minimum length may vary based on cable configuration
General Specifications	
Color, boot A	Blue
Color, connector A	Blue
Interface, Connector A	SC/UPC
Jacket Color	Yellow
Total Fibers, quantity	1
Dimensions	
Cable Assembly Length Range (m)	1 – 20

TeraSPEED® SC/UPC to Unconnectorized, Fiber Pigtail, 0.9 mm SBJ

Ordering Tree

Cable Assembly Length Range (ft)

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

1 - 66



# FBWSCUC11

Jacket Color Breakout Length / Option			
	ι	UOM	Length
J Yellow X No breakout	F	Feet	

## Mechanical Specifications

Cable Retention Strength, maximum	2.00 lb @ 90 °   5.00 lb @ 0 °
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.652.D   G.657.A1, TeraSPEED®

### **Environmental Specifications**

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Dual Rated LSZH/Riser

2

### Packaging and Weights

Packaging	quantity	
-----------	----------	--

### Regulatory Compliance/Certifications

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



### Included Products

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024



# FBWSCUC11

760004564 N-001-RF-8W-F09YL	-	Fiber Indoor Cable, TeraSPEED® 0.9 mm Low Smoke Zero Halogen Reinforced Buffered, 1 fiber, Singlemode G.652.D and G.657.A1, Gel-free, Feet jacket marking, Yellow jacket color
860648962	-	SC/UPC Connector, Singlemode, Blue

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2024

