

# L4-HMHM-20M-SGW-D

---



D-CLASS LDF4-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Male with HELIAX® SureGuard weatherproofing, 20 m

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

|                       |                                |
|-----------------------|--------------------------------|
| <b>Product Type</b>   | SureFlex® D-CLASS, dynamic PIM |
| <b>Product Series</b> | LDF4-50A                       |

## General Specifications

|   |             |
|---|-------------|
| <b>Body Style, Connector A</b>            | Straight    |
| <b>Body Style, Connector B</b>            | Straight    |
| <b>Interface, Connector A</b>             | 4.3-10 Male |
| <b>Interface, Connector B</b>             | 4.3-10 Male |
| <b>Specification Sheet Revision Level</b> | B           |

## Dimensions

|                     |                  |
|---------------------|------------------|
| <b>Length</b>       | 20 m   65.617 ft |
| <b>Nominal Size</b> | 1/2 in           |

## Electrical Specifications

|  |                                    |
|--|------------------------------------|
| <b>3rd Order IMD Dynamic</b>             | -119 dBm                           |
| <b>3rd Order IMD Dynamic Test Method</b> | Two +43 dBm carriers per IEC 62037 |
| <b>DTF, Connector A</b>                  | -34 dB                             |
| <b>DTF, Connector B</b>                  | -34 dB                             |

## Logo Image

# L4-HMHM-20M-SGW-D



## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698-960 MHz    | 1.101 | 26.36            |
| 1700-2200 MHz  | 1.101 | 26.36            |
| 2200-2700 MHz  | 1.135 | 23.98            |
| 3400-3800 MHz  | 1.222 | 20.01            |

## Jumper Assembly Sample Label

Batch Manufacturing Date (two digit year and week)

Manufacturing Plant Product Revision

0123456789 US22 1240 /A

COMMSCOPE Andrew Solutions™

**F4-DMDM-2M-D** Part Number

2 M (6.562 FT)  
SUREFLEX ASSEMBLY  
U.S. PATENT 5802710  
Product of UNITED STATES

12US220001242 Serial Number



# L4-HMHM-20M-SGW-D

---

## Environmental Specifications

**Immersion Test Method** Meets IEC 60529:2001, IP68 in mated condition

**Weatherproofing Method** HELIAX® SureGuard weatherproofing boot

## Packaging and Weights

**Included** Weatherproofing boot

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

