

# 3600000015 | 12.7mm/10mm PLENUM DUCT EMPTY

E20t® Empty Conduit, 12.7 mm, opaque white



## Product Classification

Product Type	Empty conduit
Product Brand	E20®
Warranty	One year

## General Specifications

Color	Opaque white
Conduit Type	Non-toneable
Density, maximum	0.955 g/cm³   0.035 lb/in³
Density, minimum	0.941 g/cm³   0.034 lb/in³
Design Standard	ASTM D3350-05
Wall Type	Smooth

## Dimensions

Inner Diameter, nominal	9.398 mm   0.37 in
Outer Diameter, nominal	12.7 mm   0.5 in
Wall Thickness, minimum	1.067 mm   0.042 in
Nominal Size	12.7 mm

## Material Specifications

Material Type	PVDF
---------------	------

## Mechanical Specifications

Minimum Bend Radius, unsupported	330.2 mm   13 in
Tensile Strength at yield, minimum	20.684 N/mm²   3000 psi
Pulling Tension, maximum	80.286 kg   177 lb

# 360000015 | 12.7mm/10mm PLENUM DUCT EMPTY

---

## Environmental Specifications

**Flame Test Listing** UL 94 V-0

## Packaging and Weights

**Weight, net** 72.92 kg/km | 49 lb/kft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines