



iPatch® 600A Fixed Multimode Intelligent Fiber Panel, SC 12 port duplex

OBSOLETE

This product was discontinued on: December 31, 2012

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch®
Product Type	Fiber patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Mode	Multimode
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)

Dimensions

Depth	223.52 mm 8.80 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in
Weight	1.81 kg 4.00 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Rack Units	1.0
Shelf Movement	Fixed
Color	Black
Includes	Cover Four #12-24 mounting screws Instruction sheet One piece double sided tape One set splice tray holders Shelf Two cable ties Two wire retainers
Interface, front	SC
Package Quantity	1

Total Ports, quantity 12

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

