



## HELIAX® FiberFeed® Outdoor Excess Cable Enclosure, 18 in x 18 in x 4 in

### Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	FiberFeed®   HELIAX®
<b>Product Type</b>	Outdoor junction box
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Construction Materials

<b>Material Type</b>	Aluminum
----------------------	----------

### Dimensions

<b>Depth</b>	101.60 mm   4.00 in
<b>Height</b>	465.46 mm   18.33 in
<b>Width</b>	457.20 mm   18.00 in
<b>Weight</b>	4.46 kg   9.84 lb

### Environmental Specifications

<b>Environmental Space</b>	Indoor   Outdoor
<b>Qualification Standards</b>	IEC 60529:2001, IP64

### General Specifications

<b>Application</b>	Accepts 30 m of excess fiber trunk cable
<b>Color</b>	Gray
<b>Includes</b>	Mounting kit

### Mechanical Specifications

<b>Cable Entry, quantity, maximum, left</b>	1
<b>Cable Entry, quantity, maximum, right</b>	1
<b>Mount Type</b>	Pipe, 76.2 mm (3 in) OD   Wall

### Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

