



Single Phase Meter Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Power supply enclosure

Dimensions

Depth 254 mm | 10 in
Depth, without door 254 mm | 10 in
Height 1015 mm | 40 in
Width 655 mm | 26 in
Weight 36 kg | 79 lb

General Specifications

Access Front door
Accessories Cable plate | In-ground root | Plinth
Batteries Supported 0
Batteries Supported, with optional battery pedestal 0
Cabinet Type Meter cabinet
Color Green
Door Security 7 mm triangle lock
Finish Powder coated
Internal Mounting Surface 12 mm plywood backboard
Material Type Galvanized steel

Unit Options

Color Gray RAL7035 | Green RAL6009 | Others available at additional cost

Electrical Specifications

ac Distribution Type 10-way metal enclosure
ac Feeds, Outgoing, quantity 6
Generator Connection No connection

Power Phase

Single

Voltage

230 Vac

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

