

Fiber Optic MPO-LC Module, XG, 6 ports, orange

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OM3
<b>Fiber Mode</b>	Multimode

## Dimensions

<b>Depth</b>	114.30 mm   4.50 in
<b>Height</b>	28.96 mm   1.14 in
<b>Width</b>	129.54 mm   5.10 in

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	12
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Black
<b>Adapter Color</b>	Orange
<b>Adapters, quantity, front</b>	6
<b>Body Style</b>	Duplex   Straight orientation
<b>Color, housing</b>	Black
<b>Packaging Type</b>	Bag   Carton
<b>Polarity</b>	Pairs, flipped
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Standard
<b>Color, rear</b>	Black
<b>Package Quantity</b>	1

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

