

Fiber Optic Termination Panel, 3U, 19 in, unloaded, 48-fiber, black

OBSOLETE

This product was discontinued on: December 31, 2017

Replaced By

760231498
SD-4U-FX

Standard Density 4U fixed Panel, accepts (12) LGX/1000 style footprint modules or panels, providing up to 144 duplex LC ports

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber patch panel
Regional Availability	Asia Latin America North America

Construction Materials

Finish	Powder coated
Material Type	Aluminum

Dimensions

Height	88.90 mm 3.50 in
Width	304.80 mm 12.00 in

General Specifications

Rack Units	3.0
Body Style	Symmetrical
Color	Black
Color, front	Black
Growth Configuration	Unloaded
Includes	Mounting hardware
Package Quantity	1
Rack Type	EIA 19 in
Total Ports, quantity	48

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

