



FMT MicroVAM Fiber Optic Module, CWDM, 4 channels, mux/demux, SC/APC, starting wavelength 1611 nm, 1310 nm upgrade port

Product Classification

Product Type	CWDM module
Product Series	FMT
Regional Availability	North America

General Specifications

Distribution Type	4-channel CWDM
Interface, input	LC
Interface, output	LC
Application	For use with FMT panels For use with NGF frames
Circuits, quantity	1
Functionality	Demultiplexing Multiplexing
Interface Feature, input	Standard
Interface Feature, output	Standard
Multiplexers, quantity	1
Package, quantity	1
Port Type, optional	Upgrade port

Dimensions

Depth	177.80 mm 7.00 in
Height	71.88 mm 2.83 in
Width	17.27 mm 0.68 in

Mechanical Specifications

Device Type	Micro VAM
Access	Front

Optical Specifications

Starting Wavelength	1611.00 nm
----------------------------	------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

