



Fiber Optic Termination Panel, fixed tray, 1 RU, 19 in, unloaded, 12/24-port, black

**OBSOLETE**

## Product Classification

<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	Australia/New Zealand

## Dimensions

<b>Depth</b>	295.00 mm   11.61 in
<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	375.00 mm   14.76 in
<b>Weight</b>	6.40 kg   14.11 lb

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)

## General Specifications

<b>Rack Units</b>	1.0
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Includes</b>	Mounting hardware
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Total Ports, quantity</b>	24
<b>Transmission Standards</b>	AS/NZS 2211.1   IEC 60852-1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
---------------	-----------------------

RoHS 2011/65/EU

Compliant

