



Hercules Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Macro cell site enclosure

Dimensions

Depth 550 mm | 22 in
Height 1570 mm | 62 in
Weight 400 kg | 882 lb
Width 1898 mm | 75 in

General Specifications

Access Front door | Side door
Batteries Supported 4
Battery String Current, maximum 44 A-h @ 48 Vdc
Cabinet Type Integrated cabinet
Color Green
Cooling Options 175 mm fan (3)
Door Security Swing handle with 22mm profile cylinder
Doors, quantity 3
Finish Powder coated
Includes -48V DC Power supply unit | Batteries | Brackets | Cooling | Power Distribution
Material Type Galvanized steel
Ordering Note For UK region only
Rack Type EIA 19 in
Rack Units 13

Unit Options

Color Gray RAL7035 | Green RAL6009 | Others available at additional cost

Electrical Specifications

A-100451

ac Distribution Type	10-way metal enclosure
dc Distribution Type	8-way dc panel Power supply unit
Generator Connection	No connection
Input Power Supply	50 A
Power Phase	Single
Rectifier Power	3 kW
Rectifiers, quantity	3
Voltage	230 Vac

Mechanical Specifications

Mounting Plinth | Root

Environmental Specifications

Qualification Standards IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP55

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

