



Mini G Cabinet

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type Micro cell site enclosure

Dimensions

Depth 352 mm | 14 in
Height 1032 mm | 41 in
Weight 130 kg | 287 lb
Width 1030 mm | 41 in

General Specifications

Access Front door | Side door
Batteries Supported 0
Cabinet Type Integrated cabinet
Color Green
Cooling Options 175 mm fan (1)
Door Security Swing handle with 22mm profile cylinder
Doors, quantity 2
Finish Powder coated
Includes -48V DC Power supply unit | Brackets | Cooling | Installation Kit | Power Distribution
Material Type Galvanized steel
Ordering Note For UK region only
Rack Type EIA 19 in
Rack Units 4

Unit Options

Color Gray RAL7035 | Green RAL6009 | Others available at additional cost

Electrical Specifications

ac Distribution Type 8-way plastic enclosure

dc Distribution Type	Power supply unit
Generator Connection	No connection
Input Power Supply	16-20A
Power Phase	Single
Rectifier Power	800 W
Rectifiers, quantity	2
Voltage	230 Vac

Mechanical Specifications

Mounting Plinth | Root

Environmental Specifications

Qualification Standards IEC 60529: 2001 | IEE Wiring Regulations BS 7671 | IP55

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

