



## Link ac Cabinet, Mark 4

- Sealed to outside environment
- Double wall construction

## Product Classification

**Product Type** Power supply enclosure

## Dimensions

**Depth** 520 mm | 20 in  
**Height** 1535 mm | 60 in  
**Width** 600 mm | 24 in  
**Weight** 150 kg | 331 lb

## General Specifications

**Access** Front door  
**Batteries Supported** 0  
**Cabinet Type** Integrated cabinet  
**Color** Green  
**Cooling Options** 175 mm fan (1)  
**Door Security** European profile cylinder  
**Doors, quantity** 2  
**Finish** Powder coated  
**Includes** -48V DC Power supply unit | Brackets | Cooling | Installation Kit | Power Distribution  
**Material Type** Galvanized steel  
**Ordering Note** For UK region only  
**Rack Type** EIA 19 in  
**Rack Units** 13

## Unit Options

**Color** Gray RAL7035 | Green RAL6009 | Others available at additional cost

## Electrical Specifications

**ac Distribution Type** 20-way plastic enclosure

<b>dc Distribution Type</b>	8-way dc panel   Power supply unit
<b>Generator Connection</b>	No connection
<b>Input Power Supply</b>	100 A
<b>Power Phase</b>	Single
<b>Rectifier Power</b>	800 W
<b>Rectifiers, quantity</b>	2
<b>Voltage</b>	230 Vac

## Mechanical Specifications

<b>Mounting</b>	Plinth   Root
-----------------	---------------

## Environmental Specifications

<b>Qualification Standards</b>	IEC 60529: 2001   IEE Wiring Regulations BS 7671   IP55
--------------------------------	---------------------------------------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

