

FDF Fiber Termination Panel, 144 LC/UPC, singlemode, 8 in x 23 in, putty white, pre-terminated with IFC cable, 50 meters, Stub tail at far end

## Product Classification

<b>Product Series</b>	FDF
<b>Product Type</b>	Fiber patch panel, with IFC cable
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Cable Stub Length</b>	150 m   492 ft
<b>Depth</b>	304.80 mm   12.00 in
<b>Height</b>	203.20 mm   8.00 in
<b>Width</b>	584.20 mm   23.00 in

## General Specifications

<b>Rack Units</b>	4.6
<b>Shelf Movement</b>	Fixed
<b>Application</b>	Used in rear-load FDF-style frames only
<b>Body Style</b>	Symmetrical
<b>Cable Stub Type</b>	IFC
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Interface Feature, front</b>	LC/UPC
<b>Interface, front</b>	LC
<b>Interface, rear</b>	Stub tail
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 23 in
<b>Total Ports, quantity</b>	144

## Mechanical Specifications

<b>Cable Exit Location</b>	Upward
----------------------------	--------

**Patch Cord Entry Location** Front, left side | Front, right side

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

