



FIST-GSS2 Fiber Splice Panel, 3RU, 19 in, gray

Product Classification

| | |
|------------------------------|--------------------|
| Brand | FIST™ |
| Product Series | FIST-GSS2 |
| Product Type | Fiber splice panel |
| Regional Availability | EMEA |

Construction Materials

| | |
|----------------------|------------------|
| Finish | Powder coated |
| Material Type | Galvanized steel |

Dimensions

| | |
|---------------|----------------------|
| Height | 133.35 mm 5.25 in |
| Width | 482.60 mm 19.00 in |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -5 °C to +45 °C (+23 °F to +113 °F) |
| Relative Humidity | Up to 93%, non-condensing |
| Storage Temperature | -30 °C to +60 °C (-22 °F to +140 °F) |

General Specifications

| | |
|-------------------------|------------------------------------|
| Rack Units | 3.0 |
| Shelf Movement | Sliding |
| Application | Used in FIST-GR3-style frames only |
| Color | Gray |
| Color, front | Gray |
| Functionality | Splicing |
| Includes | Mounting hardware |
| Package Quantity | 1 |
| Rack Type | EIA 19 in ETSI 600 mm |

Regulatory Compliance/Certifications

| | |
|---------------|-----------------|
| Agency | RoHS 2011/65/EU |
|---------------|-----------------|

| | |
|-----------------------|-----------|
| Classification | Compliant |
|-----------------------|-----------|

