

FL2000 Fiber Termination Panel, 96 SC/UPC, singlemode, 6RU, 19 in, putty white

## Product Classification

<b>Product Series</b>	FL2000
<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Depth</b>	256.54 mm   10.10 in
<b>Height</b>	266.70 mm   10.50 in
<b>Width</b>	482.60 mm   19.00 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Rack Units</b>	6.0
<b>Shelf Movement</b>	Hinged
<b>Adapter Packs Included, quantity</b>	8
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Includes</b>	Mounting hardware
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	SC
<b>Package Quantity</b>	1
<b>Patching Capacity, maximum</b>	96
<b>Rack Type</b>	EIA 19 in
<b>Splicing Capacity, maximum</b>	0
<b>Total Ports, quantity</b>	96

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

