

FL2000 Fiber Termination Panel, 24 SC/UPC, singlemode, 2RU, 23 in, putty white, pre-terminated with OSP cable, 150 feet, Stub tail at far end

Product Classification

Product Series	FL2000
Product Type	Fiber patch panel, with OSP cable
Regional Availability	Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Cable Stub Length	46 m 150 ft
Depth	256.54 mm 10.10 in
Height	88.90 mm 3.50 in
Width	584.20 mm 23.00 in

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Rack Units	2.0
Shelf Movement	Hinged
Adapter Packs Included, quantity	4
Cable Stub Type	IFC
Color	Putty white
Color, front	Putty white
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	Standard
Interface, front	SC
Interface, rear	Stub tail
Package Quantity	1
Patching Capacity, maximum	24
Rack Type	EIA 23 in

Splicing Capacity, maximum 0
Total Ports, quantity 24

Mechanical Specifications

Cable Exit Location Downward

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

