

FL2000 Fiber Termination Panel, 144 LC/UPC, singlemode, 5RU, 23 in, putty white, pre-terminated with IFC cable, 100 feet, Stub tail at far end

## Product Classification

<b>Product Series</b>	FL2000
<b>Product Type</b>	Fiber patch panel, with IFC cable
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Singlemode
<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Dimensions

<b>Cable Stub Length</b>	30 m   100 ft
<b>Depth</b>	256.54 mm   10.10 in
<b>Height</b>	222.25 mm   8.75 in
<b>Width</b>	584.20 mm   23.00 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Rack Units</b>	5.0
<b>Shelf Movement</b>	Hinged
<b>Adapter Packs Included, quantity</b>	12
<b>Cable Stub Type</b>	IFC
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Functionality</b>	Patching
<b>Growth Configuration</b>	Fully loaded
<b>Interface Feature, front</b>	Standard
<b>Interface, front</b>	LC
<b>Interface, rear</b>	Stub tail
<b>Package Quantity</b>	1
<b>Patching Capacity, maximum</b>	144
<b>Rack Type</b>	EIA 23 in

**Splicing Capacity, maximum** 0  
**Total Ports, quantity** 144

## Mechanical Specifications

**Cable Exit Location** Downward

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

