

LSX Fiber Termination Panel with OSP cable, 9 in x 19 in, 144 SC/UPC, singlemode, putty white, 16 meters, Stub tail at far end

Product Classification

Product Series	LGX
Product Type	Fiber patch panel, with OSP cable
Regional Availability	Latin America North America

Construction Materials

Fiber Mode	Singlemode
Finish	Powder coated
Material Type	Steel

Dimensions

Cable Stub Length	16 m 52 ft
Depth	304.80 mm 12.00 in
Height	228.60 mm 9.00 in
Width	482.60 mm 19.00 in

General Specifications

Rack Units	5.1
Shelf Movement	Fixed
Application	Used in LSX-style frames only
Body Style	Symmetrical
Cable Stub Type	OSP
Color	Putty white
Color, front	Putty white
Functionality	Patching
Growth Configuration	Fully loaded
Interface Feature, front	Standard
Interface, front	SC
Interface, rear	Stub tail
Package Quantity	1
Rack Type	EIA 19 in EIA 23 in
Total Ports, quantity	144

Mechanical Specifications

Cable Exit Location	Upward
----------------------------	--------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

