

# 760242261 | Straight Integrated Pole 5G



Straight 12inch diameter, Integrated Concealment Pole for 5G deployments, to mount and conceal mmWave active antennas, radios and other wireless infrastructure equipment in pole modules.

- Intended to mount and conceal mmWave active antennas and infrastructure equipment utilizing pole modules
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- For 5G radios, integrated AC load center/OVP and Disconnect

## Product Classification

**Product Type** Metro cell site enclosure

## Dimensions

**Depth** 323.9 mm | 12.8 in  
**Depth Note** Round  
**Height Note** 8 ft tall Power Module Base  
**Pole Diameter** 323.9 mm | 12.8 in  
**Pole Height Options** 20.0 ft | 25.0 ft | 30.0 ft | 35.0 ft | 40.0 ft

## General Specifications

**Color** Light Grey (RAL 7035)  
**Color Notes** 760242261AB1HH - Light Grey | 760242261AB2HH - Green | 760242261AB3HH - Black | 760242261AB4HH - Brown | 760242261AB5HH- Beige-Grey | 760242261AB9HH - Metallic Silver | 760242261ABCCH - Faux Concrete | 760242261ABWHH - Pure White  
**Color Options** Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White  
**Finish Aluminum** Chromate  
**Finish Concealment Covers** Powder coated  
**Material** Steel

## Electrical Specifications

**Power/Fiber Input** AC load center with OVP and disconnect

## Antenna Specifications

**Antenna Compatibility, CommScope** mmWave active antennas  
**Antenna Compatibility, Other Vendors** mmWave active antennas  
**Antennas Included** None

## Radio Specifications

<b>Radio Compatibility, Ericsson</b>	(3) AIR 5121/5331 (Upgradeable to AIR 6701)   760242261E
<b>Radio Compatibility, Nokia</b>	(3) AEUA (Upgradeable to AEWA)   760242261N
<b>Radios Included</b>	None

## Environmental Specifications

<b>Cooling</b>	Passive Cooling
<b>Thermal Compliance</b>	GR-487

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant



## \* Footnotes

<b>Pole Height Options</b>	Overall AGL Standard Height
----------------------------	-----------------------------