

Fiber Optic Termination Panel, 2 RU, 19 in, unloaded, 24 ports, black

## **OBSOLETE**

**This product was discontinued on: December 31, 2017**

### **Replaced By**

760231480  
SD-2U-FX

Standard Density 2U fixed Panel, accepts (6) LGX/1000 style footprint modules or panels, providing up to 72 duplex LC ports

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	Latin America   North America

## Construction Materials

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

## Dimensions

<b>Height</b>	88.90 mm   3.50 in
<b>Width</b>	304.80 mm   12.00 in

## General Specifications

<b>Rack Units</b>	2.0
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Black
<b>Growth Configuration</b>	Unloaded
<b>Includes</b>	Mounting hardware
<b>Package Quantity</b>	1
<b>Rack Type</b>	EIA 19 in
<b>Total Ports, quantity</b>	24

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

