



Bottom of the Pole, 26in Square 4G/5G capable Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Pole top concealment module for LAA/CBRS radio mounting
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Product Classification

Product Type Metro cell site enclosure

Dimensions

Depth 660.4 mm | 26.0 in
Depth Note Square
Height Note 4 ft tall Equipment Cabinet Base
Pole Diameter 203.2 mm | 8.0 in
Pole Height Options 20.0 ft | 25.0 ft | 30.0 ft | 35.0 ft | 40.0 ft

General Specifications

Color Light Grey (RAL 7035)
Color Notes 760237427AB1HH - Light Grey | 760237427AB2HH - Green | 760237427AB3HH - Black | 760237427AB4HH - Brown | 760237427AB5HH - Beige-Grey | 760237427AB9HH - Metallic Silver | 760237427ABCCH - Faux Concrete | 760237427ABWHH - Pure White
Color Options Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White
Finish Aluminum Chromate
Finish Concealment Covers Powder coated
Material Steel

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Radio Specifications

Radio Compatibility, Ericsson (1) 8843/4449 dual-band high power radio and (2) PSU-AC08 | (2) RRUS11/12/32, 2212, 4415, 4426, 4478 (base) | (3) 2203/2205/2208 (Pole Top) | 5G Expansion module included | 760237427E
Radio Compatibility, Nokia (2) Airscale dual band radios (160W or 320W and (2) Delta 1kW rectifiers (base) | (2) Airscale Micro Radios - LAA & CBRS (Pole Top) | 5G Expansion module included | 760237427N
Radios Included None

Environmental Specifications

Cooling	Fan Cooling
Thermal Compliance	GR-487

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Pole Height Options Overall AGL Standard Height