



TTRC Copper Closure, unpressurized, gel sealed, 260 mm sheath opening, for up to 25 pair splices

- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensing mechanism

Product Classification

Product Type	Gel sealed closure
Product Series	TTRC
Regional Availability	EMEA

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	4
Color	Black
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	19.00 mm 0.75 in
Single Cable Diameter, minimum	10.00 mm 0.39 in
Splice Bundle Diameter, maximum	72.00 mm 2.83 in
Splicing Capacity, maximum	25

Dimensions

Sheet Opening, nominal	260.00 mm 10.24 in
-------------------------------	----------------------

Mechanical Specifications

Cable Sealing Type	Gel filled
Closure Style	In-line
Mount Type	Strand

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

RoHS 2011/65/EU

Compliant

