



MJC Copper Closure, unpressurized, gel sealed, cap-ended, for up to 50/100 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Flexible branching plug system allowing installation of cables from 5-pair to 100pair
- Reduced inventory as fewer size closures needed to cover a wide range of applications up to 100 pairs

## Product Classification

<b>Product Type</b>	Gel sealed closure
<b>Product Series</b>	MJC
<b>Regional Availability</b>	EMEA

## General Specifications

<b>Application</b>	For use with Polyethylene cables
<b>Cable Capacity, maximum</b>	4
<b>Color</b>	Black
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Single Cable Diameter, maximum</b>	28.00 mm   1.10 in
<b>Single Cable Diameter, minimum</b>	7.00 mm   0.28 in
<b>Splice Bundle Diameter, maximum</b>	120.00 mm   4.72 in
<b>Splicing Capacity, maximum</b>	50

## Dimensions

<b>Length</b>	185.00 mm   7.28 in
---------------	---------------------

## Mechanical Specifications

<b>Cable Sealing Type</b>	Gel filled
<b>Closure Style</b>	Single-ended

## Environmental Specifications

<b>Environmental Space</b>	Aerial   Buried
----------------------------	-----------------

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

