



MJC Copper Closure, unpressurized, gel sealed, in-line, for up to 50/100 pair splices

- Watertight splice closure for aerial, underground and direct buried splices in the unpressurized copper telecommunication network
- Flexible branching plug system allowing installation of cables from 5-pair to 100pair
- Reduced inventory as fewer size closures needed to cover a wide range of applications up to 100 pairs

Product Classification

Product Type	Gel sealed closure
Product Series	MJC
Regional Availability	EMEA

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	4
Color	Black
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	28.00 mm 1.10 in
Single Cable Diameter, minimum	7.00 mm 0.28 in
Splice Bundle Diameter, maximum	90.00 mm 60.00 mm
Splicing Capacity, maximum	50

Dimensions

Length	370.00 mm 14.57 in
---------------	----------------------

Mechanical Specifications

Cable Sealing Type	Gel filled
Closure Style	Single-ended

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification	Compliant
-----------------------	-----------

