



GS3 1650 B2 Copper Splice Closure, cold applied, for cables up to 400 pairs

- Cold applied buried and pedestal splice closure system providing a fast, simple way to seal and encapsulate telephone cable splices
- Material is composed of several layers of specially blended polymers and gels and an aluminum moisture vapor barrier layer
- Outer compression wrap provides excellent mechanical strength and superior protection from forces such as impact and abrasion
- Innovative Urethane Delivery System drives encapsulant into the core of the cable, providing protection superior to that of traditional poured urethane systems

## Product Classification

<b>Product Type</b>	Sealing sheet closure
<b>Product Series</b>	GS3
<b>Regional Availability</b>	Latin America   North America

## General Specifications

<b>Color</b>	Black
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Required Encapsulant, minimum</b>	3000 g   7 lb
<b>Splice Bundle Diameter, maximum</b>	95.25 mm   3.75 in
<b>Splicing Capacity, maximum</b>	400

## Dimensions

<b>Sheet Opening, nominal</b>	533.40 mm   21.00 in
-------------------------------	----------------------

## Mechanical Specifications

<b>Cable Sealing Type</b>	Multilayer gel sealing sheet
<b>Closure Style</b>	In-line

## Environmental Specifications

<b>Environmental Space</b>	Buried
----------------------------	--------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

