



GS3 1650 C2 Copper Splice Closure, cold applied, for cables up to 900 pairs

- Cold applied buried and pedestal splice closure system providing a fast, simple way to seal and encapsulate telephone cable splices
- Material is composed of several layers of specially blended polymers and gels and an aluminum moisture vapor barrier layer
- Outer compression wrap provides excellent mechanical strength and superior protection from forces such as impact and abrasion
- Innovative Urethane Delivery System drives encapsulant into the core of the cable, providing protection superior to that of traditional poured urethane systems

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Product Type</b>          | Sealing sheet closure         |
| <b>Product Series</b>        | GS3                           |
| <b>Regional Availability</b> | Latin America   North America |

## General Specifications

|  |                     |
|--|---------------------|
| <b>Color</b>                           | Black               |
| <b>Package, quantity</b>               | 1                   |
| <b>Packaging Type</b>                  | Bag   Carton        |
| <b>Required Encapsulant, minimum</b>   | 5000 g   11 lb      |
| <b>Splice Bundle Diameter, maximum</b> | 134.62 mm   5.30 in |
| <b>Splicing Capacity, maximum</b>      | 900                 |

## Dimensions

|                               |                      |
|-------------------------------|----------------------|
| <b>Sheet Opening, nominal</b> | 533.40 mm   21.00 in |
|-------------------------------|----------------------|

## Mechanical Specifications

|                           |                              |
|---------------------------|------------------------------|
| <b>Cable Sealing Type</b> | Multilayer gel sealing sheet |
| <b>Closure Style</b>      | In-line                      |

## Environmental Specifications

|                            |        |
|----------------------------|--------|
| <b>Environmental Space</b> | Buried |
|----------------------------|--------|

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

