



GS3 1650 PED Copper Splice Closure, cold applied, for cables in pedestal up to 100 pairs

- Cold applied buried and pedestal splice closure system providing a fast, simple way to seal and encapsulate telephone cable splices
- Material is composed of several layers of specially blended polymers and gels and an aluminum moisture vapor barrier layer
- Outer compression wrap provides excellent mechanical strength and superior protection from forces such as impact and abrasion
- Innovative Urethane Delivery System drives encapsulant into the core of the cable, providing protection superior to that of traditional poured urethane systems

Product Classification

| | |
|------------------------------|-------------------------------|
| Product Type | Sealing sheet closure |
| Product Series | GS3 |
| Regional Availability | Latin America North America |

General Specifications

| | |
|-----------------------------------|--------------|
| Color | Black |
| Package, quantity | 1 |
| Packaging Type | Bag Carton |
| Splicing Capacity, maximum | 100 |

Mechanical Specifications

| | |
|---------------------------|------------------------------|
| Cable Sealing Type | Multilayer gel sealing sheet |
| Closure Style | Single-ended |
| Mount Type | Pedestal |

Environmental Specifications

| | |
|----------------------------|-----------------------------|
| Environmental Space | Above ground Below ground |
|----------------------------|-----------------------------|

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

