



GS3 1650 PED Copper Splice Closure, cold applied, for cables in pedestal up to 300 pairs

- Cold applied buried and pedestal splice closure system providing a fast, simple way to seal and encapsulate telephone cable splices
- Material is composed of several layers of specially blended polymers and gels and an aluminum moisture vapor barrier layer
- Outer compression wrap provides excellent mechanical strength and superior protection from forces such as impact and abrasion
- Innovative Urethane Delivery System drives encapsulant into the core of the cable, providing protection superior to that of traditional poured urethane systems

Product Classification

Product Type	Sealing sheet closure
Product Series	GS3
Regional Availability	Latin America North America

General Specifications

Color	Black
Package, quantity	1
Packaging Type	Bag Carton
Splicing Capacity, maximum	300

Mechanical Specifications

Cable Sealing Type	Multilayer gel sealing sheet
Closure Style	Single-ended
Mount Type	Pedestal

Environmental Specifications

Environmental Space	Above ground Below ground
----------------------------	-----------------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

