



PEDCAP Copper Closure, butt, unpressurized, heat shrink, 250 mm joint length, for up to 4 cables

- One piece end cap with heat-shrinkable outlet for sealing onto the cables
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network
- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications

Product Classification

Product Type	Unpressurized heat shrink closure
Product Series	PEDCAP
Regional Availability	EMEA

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	4
Color	Black
Includes	Aluminum closing strip Aluminum foil Cleaning tissues Desiccant Tie wraps
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	60.00 mm 2.36 in
Single Cable Diameter, minimum	25.00 mm 0.98 in
Splice Bundle Diameter, maximum	84.00 mm 3.31 in
Splicing Capacity, maximum	200

Dimensions

Length	360.00 mm 14.17 in
Sheet Opening, nominal	250.00 mm 9.84 in

Mechanical Specifications

Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Material Type	Polyolefin
Mount Type	Pedestal

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

