



RABC Copper Closure, butt, unpressurized, heat shrink, 480 mm joint length, for up to 4 cables

- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network

Product Classification

Product Type	Unpressurized heat shrink closure
Product Series	RABC
Regional Availability	EMEA

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	4
Color	Black
Includes	Abrasive strip Aluminum foil Branch-off clip Clamp O-ring seal Tie wraps
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	125.00 mm 4.92 in
Single Cable Diameter, minimum	43.00 mm 1.69 in
Splice Bundle Diameter, maximum	100.00 mm 3.94 in

Dimensions

Length	670.00 mm 26.38 in
Sheet Opening, nominal	480.00 mm 18.90 in

Mechanical Specifications

Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Material Type	Polyolefin

Environmental Specifications

Environmental Space	Aerial Buried
----------------------------	-----------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

