



VCKT Vault Copper Closure, unpressurized, heat shrink, 740 mm joint length, 12 MDF cable outlets

- Vault closure system for the distribution of telecommunication cables in telephone exchanges
- Flexibility arises from selective use of break-out ports up to 3/9/12 or 24 MDF cables
- Vertical installation with re-entry option of the splice area for testing and measuring

## Product Classification

<b>Product Type</b>	Unpressurized heat shrink closure
<b>Product Series</b>	VCKT
<b>Regional Availability</b>	EMEA

## General Specifications

<b>Application</b>	For use with Polyethylene and metal jacketed cables
<b>Branch-off Clip</b>	To be ordered separately
<b>Cable Capacity, maximum</b>	13
<b>Color</b>	Black
<b>Includes</b>	Abrasive strip   Aluminum closing strip   Aluminum foil   Cleaning tissues   Flexible stainless steel channels   Heatshrinkable sleeve   Metal canister   Shield continuity wire   Underclips
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Bag   Carton
<b>Single Cable Diameter, maximum</b>	36.00 mm   1.42 in
<b>Single Cable Diameter, minimum</b>	12.00 mm   0.47 in
<b>Splice Bundle Diameter, maximum</b>	158.00 mm   6.22 in

## Dimensions

<b>Length</b>	950.00 mm   37.40 in
<b>Sheet Opening, nominal</b>	740.00 mm   29.13 in

## Dimension Drawing

<b>Dimension Drawing</b>	Used as an image placeholder
--------------------------	------------------------------

## Mechanical Specifications

<b>Cable Sealing Type</b>	Hotmelt adhesive
<b>Closure Style</b>	Single-ended
<b>Splice Protection Type</b>	Metal canister

## Environmental Specifications

**Environmental Space**

Above ground | Below ground | Buried

Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

