



VCKT Vault Copper Closure, unpressurized, heat shrink, 740 mm joint length, 24 MDF cable outlets

- Vault closure system for the distribution of telecommunication cables in telephone exchanges
- Flexibility arises from selective use of break-out ports up to 3/9/12 or 24 MDF cables
- Vertical installation with re-entry option of the splice area for testing and measuring

Product Classification

Product Type	Unpressurized heat shrink closure
Product Series	VCKT
Regional Availability	EMEA

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered separately
Cable Capacity, maximum	25
Color	Black
Includes	Abrasive strip Aluminum closing strip Aluminum foil Cleaning tissues Flexible stainless steel channels Heatshrinkable sleeve Metal canister Shield continuity wire Underclips
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	36.00 mm 1.42 in
Single Cable Diameter, minimum	12.00 mm 0.47 in
Splice Bundle Diameter, maximum	196.00 mm 7.72 in

Dimensions

Length	950.00 mm 37.40 in
Sheet Opening, nominal	740.00 mm 29.13 in

Dimension Drawing

Dimension Drawing	Used as an image placeholder
--------------------------	------------------------------

Mechanical Specifications

Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Splice Protection Type	Metal canister

Environmental Specifications

Environmental Space

Above ground | Below ground | Buried

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

