



OCM1 LGX Fiber Optic Module, DWDM, Mux, SC/UPC, 8 channels, upgrade port, starting wavelength 1553.33 nm

## Product Classification

<b>Product Type</b>	DWDM module
<b>Product Series</b>	LGX   OCM1
<b>Regional Availability</b>	North America

## General Specifications

<b>Distribution Type</b>	8-channel DWDM
<b>Interface, input</b>	SC
<b>Interface, output</b>	SC
<b>Application</b>	For use with LGX panels
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Multiplexing
<b>Interface Feature, input</b>	Standard
<b>Interface Feature, output</b>	Standard
<b>Multiplexers, quantity</b>	1
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Port Type, optional</b>	Upgrade port

## Dimensions

<b>Depth</b>	127.00 mm   5.00 in
<b>Height</b>	129.54 mm   5.10 in
<b>Width</b>	58.42 mm   2.30 in

## Mechanical Specifications

<b>Device Type</b>	Standard VAM
--------------------	--------------

## Optical Specifications

<b>Starting Wavelength</b>	1553.33 nm
----------------------------	------------

**Channel Spacing** 100 GHz

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

