



MPO Trunk Cable, Multimode, 24 fibers, MPO to MPO, aqua, 10 m

Product Classification

Portfolio	NETCONNECT®
Brand	MPOptimate®
Product Type	Fiber trunk cable assembly
Regional Availability	Latin America North America

Construction Materials

Fiber Type	OM3
Total Fibers, quantity	24
Jacket Color	Aqua
Fiber Mode	Multimode

Dimensions

Cord Length	10.00 m 32.81 ft
Diameter Over Jacket	8.00 mm 0.31 in

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

General Specifications

Interface, connector A	MPO-12/UPC Female
Interface, connector B	MPO-12/UPC Female
Color, connector A	Beige
Color, connector B	Beige
Color, boot A	Black
Color, boot B	Black
Connector A, quantity	2
Connector B, quantity	2
Package Quantity	1
Polarity	Pairs, flipped

Optical Performance

1-1859491-0

Insertion Loss, maximum, connector A 0.35 dB

Insertion Loss, maximum, connector B 0.35 dB

Return Loss, minimum, connector A 28.00 dB

Return Loss, minimum, connector B 28.00 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

