



## High-Density Front-Loading Cable Manager, 6U

- Offers bend radius and mechanical protection
- Suitable for Twisted Pair and Fiber Optic patch cords
- Rubber entry/exit retainers ensure cable captivity preventing accidental disturbance of patch cords

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Cable management hardware   |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Depth</b>  | 150.00 mm   5.91 in  |
| <b>Height</b> | 266.05 mm   10.47 in |
| <b>Width</b>  | 62.50 mm   2.46 in   |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Safety Standard</b>       | cUL   UL                             |

## General Specifications

|                               |  |
|-------------------------------|--|
| <b>Color</b>                  | Black                                  |
| <b>Rack Units</b>             | 6                                      |
| <b>Finish</b>                 | Smooth                                 |
| <b>Minimum Order Quantity</b> | 4                                      |
| <b>Ordering Note</b>          | Sold per piece with an MOQ of 4 pieces |
| <b>Package Quantity</b>       | 1                                      |

## Mechanical Specifications

|                      |                             |
|----------------------|-----------------------------|
| <b>Material Type</b> | Galvanized steel   PA   TPE |
|----------------------|-----------------------------|

## Regulatory Compliance/Certifications

|                 |                       |
|-----------------|-----------------------|
| <b>Agency</b>   | <b>Classification</b> |
| RoHS 2011/65/EU | Compliant             |

