



M81 RCA to 110 Punchdown Module Audio and Video Adapter, white housing red connector

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Multimedia outlet
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Color</b>	White
<b>Color, RCA</b>	Red
<b>Mount Type</b>	Snap-in
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

## Electrical Specifications

<b>Attenuation dc at Frequency, maximum</b>	2 dB @ 5.5 MHz
<b>Crosstalk at Frequency</b>	-60 dB @ 5.5 MHz
<b>Impedance</b>	75 ohm
<b>Insulation Resistance, minimum</b>	50 MOhm
<b>UTP 110 Terminal Block</b>	110 ohm

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Relative Humidity</b>	5%–95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

