



## ION® Active Intelligent Point of Interface Subrack with Guide Rails

**OBSOLETE**

## Product Classification

<b>Brand</b>	ION®
<b>Product Type</b>	Point of interface subrack

## General Specifications

<b>Includes</b>	Guide rails
<b>Note</b>	Detailed Product Specifications are available. Please contact your local CommScope representative.
<b>Rack Type</b>	EIA 19 in

## Electrical Specifications

<b>Electrical Safety Standard</b>	EN 60950
<b>Power Consumption</b>	276 W
<b>Voltage Range</b>	+10 to +14 Vdc

## Supervision And Control

<b>General Alarm</b>	Integrated into management system
----------------------	-----------------------------------

## Mechanical Specifications

<b>Interface Slots Available, quantity</b>	1
<b>Mounting</b>	Rack
<b>Slots Available, quantity</b>	8

## Environmental Specifications

<b>Operating Temperature</b>	+5 °C to +55 °C (+41 °F to +131 °F)
<b>Relative Humidity</b>	46%–94%
<b>Storage Temperature</b>	-25 °C to +70 °C (-13 °F to +158 °F)

## Dimensions

<b>Depth</b>	422.00 mm   16.61 in
<b>Height</b>	177.00 mm   4.00 HE
<b>Width</b>	483.00 mm   19.02 in
<b>Net Weight</b>	7.00 kg   15.43 lb

## Packed Dimensions

<b>Depth</b>	600.0 mm   23.6 in
<b>Height</b>	530.0 mm   20.9 in
<b>Width</b>	295.0 mm   11.6 in
<b>Shipping Weight</b>	8.00 kg   17.64 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

