



SYSTIMAX 360™ iPatch® G2-1U-MOD LC 5PK imVision Upgrade Kit

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	Upgrade kit
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Dimensions

Depth	12.70 mm 0.50 in
Height	31.75 mm 1.25 in
Width	393.70 mm 15.50 in
Weight	0.11 kg 0.25 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Color	Cool gray
Package Quantity	5
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

