



360G2 Multimode OM4 Standard Module, 24 LC fibers (12 duplex ports)

This product will be discontinued on: June 30, 2019

Replaced By

760206532
360DMis-24LC-LS G2 Multimode OM4 Standard Module, 24 LC fibers (12 duplex ports)

Product Classification

Portfolio CommScope®
Product Type Fiber module
Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Construction Materials

Fiber Type OM4, LazrSPEED® 550
Total Fibers, quantity 24

Dimensions

Depth 116.84 mm | 4.60 in
Height 30.48 mm | 1.20 in
Width 91.44 mm | 3.60 in

Environmental Specifications

Safety Standard UL

General Specifications

Interface, front LC
Total Ports, quantity, front 24
Interface Feature, front Standard
Color, front Aqua
Adapters, quantity, front 12
Data Module Type Standard
Intelligence Type iPatch® ready
Shuttered Yes
Interface, rear MPO Pinned

Adapters, quantity, rear	2
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 0.47 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

