

G2 Multimode OM4 Standard Module, 12 LC fibers (6 duplex ports)



This product will be discontinued on: June 30, 2019

Replaced By

760224071

360DMis-12LC-LS

G2 Multimode OM4 Standard Module, 12 LC fibers (6 duplex ports)

Product Classification

Portfolio	CommScope®
Product Type	Fiber module
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Type	OM4, LazrSPEED® 550
Total Fibers, quantity	12

Dimensions

Depth	116.84 mm 4.60 in
Height	30.48 mm 1.20 in
Width	91.44 mm 3.60 in

Environmental Specifications

Safety Standard	UL
------------------------	----

General Specifications

Interface, front	LC
Total Ports, quantity, front	12
Interface Feature, front	Standard
Color, front	Aqua
Adapters, quantity, front	6
Data Module Type	Standard
Intelligence Type	iPatch® ready
Shuttered	Yes

Interface, rear	MPO Pinned
Adapters, quantity, rear	1
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 0.47 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

