

G2 Singlemode Standard Module, 12 LC fibers (6 duplex ports)



**This product will be discontinued on: June 30, 2019**

**Replaced By**

760224089  
360DMis-12LC-SM      G2 Singlemode Standard Module, 12 LC Ports

## Product Classification

**Portfolio**                      CommScope®  
**Product Type**                Fiber module  
**Regional Availability**      Asia | Australia/New Zealand | EMEA | Latin America | North America

## Construction Materials

**Fiber Type**                    G.652.D and G.657.A1 , TeraSPEED® | OS2  
**Total Fibers, quantity**    12

## Dimensions

**Depth**                         116.84 mm | 4.60 in  
**Height**                        30.48 mm | 1.20 in  
**Width**                         91.44 mm | 3.60 in

## Environmental Specifications

**Safety Standard**             UL

## General Specifications

**Interface, front**              LC  
**Total Ports, quantity, front** 12  
**Interface Feature, front**    Standard  
**Color, front**                  Blue  
**Adapters, quantity, front** 6  
**Data Module Type**          Standard  
**Intelligence Type**          iPatch® ready  
**Shuttered**                     Yes

<b>Interface, rear</b>	MPO Pinned
<b>Adapters, quantity, rear</b>	1
<b>Interface Feature, rear</b>	Reduced footprint
<b>Color, rear</b>	Gray
<b>Package Quantity</b>	1

## Optical Performance

**Insertion Loss, maximum** 1.05 dB

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

