


G2 Singlemode APC Module, 12 LC fibers (6 duplex ports)



This product will be discontinued on: June 30, 2019

Replaced By

760224238 G2 Singlemode APC Module, 12 LC Ports
360DMis-12LCA-SM

Product Classification

Portfolio CommScope®
Product Type Fiber module
Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Construction Materials

Fiber Type G.652.D and G.657.A1 , TeraSPEED® | OS2
Total Fibers, quantity 12

Dimensions

Depth 116.84 mm | 4.60 in
Height 30.48 mm | 1.20 in
Width 91.44 mm | 3.60 in

Environmental Specifications

Safety Standard UL

General Specifications

Interface, front LC
Total Ports, quantity, front 12
Interface Feature, front APC
Color, front Green
Adapters, quantity, front 6
Data Module Type Standard
Intelligence Type iPatch® ready
Shuttered No

Interface, rear	MPO Pinned
Adapters, quantity, rear	1
Interface Feature, rear	Reduced footprint
Color, rear	Gray
Package Quantity	1

Optical Performance

Insertion Loss, maximum 1.05 dB

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

