



ION® Standard Interface Card for Active Intelligent Point of Interface

Product Classification

Brand	ION®
Product Type	Point of interface card

General Specifications

Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
-------------	----------------------------------------------------------------------------------------------------

Electrical Specifications

Electrical Safety Standard	EN 60950-1
Power Consumption	6 W
Voltage	12 Vdc

Supervision And Control

Functionality	Module alarm status Rack summary alarm status Rack/Subrack address setting
General Alarm	Integrated into management system
Management Interface	Summary alarm output

Environmental Specifications

Operating Temperature	+5 °C to +50 °C (+41 °F to +122 °F)
Relative Humidity	46%–94%
Storage Temperature	-25 °C to +70 °C (-13 °F to +158 °F)

Dimensions

Depth	422.00 mm 16.61 in
Height	172.90 mm 4.00 HE
Width	35.30 mm 1.39 in
Net Weight	0.50 kg 1.10 lb

Packed Dimensions

Depth	625.0 mm 24.6 in
Height	335.0 mm 13.2 in
Width	172.0 mm 6.8 in
Shipping Weight	1.00 kg 2.20 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

