

SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Patch Panel, 24 port



Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | iPatch® SYSTIMAX 360™ |
| Product Type | RJ45 patch panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|--|----------------------|
| Depth | 206.50 mm 8.13 in |
| Diameter Over Dielectric, maximum | 1.168 mm 0.046 in |
| Height | 44.45 mm 1.75 in |
| Width | 482.60 mm 19.00 in |

Electrical Specifications

| | |
|--|-------------------------------|
| ANSI/TIA Category | 6A |
| Current Rating at Temperature | 1.5 A @ 20 °C 1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1,500 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Safety Standard | cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|-----------------|
| Intelligence Type | iPatch® enabled |
| Total Ports, quantity | 24 |
| Cable Type | Unshielded |
| Color | Silver |
| Package Quantity | 1 |
| Rack Units | 1.0 |

Mechanical Specifications

Plug Insertion Life, minimum

750 times

Wiring

T568A | T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

