

## SYSTIMAX 360™ iPatch® 1100GS6 Evolve U/UTP Patch Panel, 48 port



## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	iPatch®   SYSTIMAX 360™
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	206.50 mm   8.13 in
<b>Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in
<b>Height</b>	89.66 mm   3.53 in
<b>Width</b>	482.60 mm   19.00 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	6A
<b>Current Rating at Temperature</b>	1.5 A @ 20 °C   1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1,500 Vac @ 60 Hz
<b>Insulation Resistance, minimum</b>	500 MOhm

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

<b>Intelligence Type</b>	iPatch® enabled
<b>Total Ports, quantity</b>	48
<b>Cable Type</b>	Unshielded
<b>Color</b>	Silver
<b>Package Quantity</b>	1
<b>Rack Units</b>	2.0

## Mechanical Specifications

**Plug Insertion Life, minimum**

750 times

**Wiring**

T568A | T568B

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

