



SYSTIMAX 360™ iPatch® Evolve High Density F/UTP Modular Panel, 48 port

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	206.50 mm 8.13 in
Diameter Over Dielectric, maximum	11.684 mm 0.460 in
Height	89.66 mm 3.53 in
Width	482.60 mm 19.00 in

Electrical Specifications

Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	48
Color	Silver
Package Quantity	1
Rack Units	2.0

Mechanical Specifications

Plug Insertion Life, minimum	750 times
-------------------------------------	-----------

Wiring

T568A | T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

