



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 24 Port, 10 pack

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Weight	0.11 kg 0.25 lb

Electrical Specifications

ANSI/TIA Category	6 6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® upgrade kit
Total Ports, quantity	24
Color	Cool gray
Package Quantity	10

Mechanical Specifications

Panel Style	Angled
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

